

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573077

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2932.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573077

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573077

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	220694
5°	224447
10°	234590
15°	248982
20°	259894
25°	257634
30°	239600
35°	204973
40°	156172
45°	91596
50°	39143
55°	11523
60°	3292
65°	1948
70°	1221
75°	1614
80°	0
85°	0



TEST NUMBER: P573077

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.7	6.0
10°-20°	554.4	18.9
20°-30°	864.9	29.5
30°-40°	841.5	28.7
40°-50°	420.3	14.3
50°-60°	65.1	2.2
60°-70°	7.9	0.3
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1595.0	54.4
0°-40°	2436.5	83.1
0°-60°	2921.9	99.7
0°-90°	2932.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2932.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1796	
5°	1820	176
15°	1958	554
25°	1901	865
35°	1367	842
45°	527	420
55°	54	65
65°	7	8
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P573077

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1796.4
2.5°	1803.1
5°	1820.0
7.5°	1846.9
10°	1880.5
12.5°	1924.0
15°	1957.6
17.5°	1984.5
20°	1987.9
22.5°	1964.4
25°	1900.6
27.5°	1806.5
30°	1689.0
32.5°	1541.4
35°	1366.7
37.5°	1175.2
40°	973.8
42.5°	758.9
45°	527.2
47.5°	339.1
50°	204.8
52.5°	110.8
55°	53.8
57.5°	23.5
60°	13.4
62.5°	10.1
65°	6.7
67.5°	6.7
70°	3.4
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)