

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573160

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1323.0 lumens
Efficiency: N/A
Efficacy: 32.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573160

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573160

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203408
5°	201472
10°	190915
15°	173331
20°	153159
25°	132409
30°	103500
35°	63470
40°	32588
45°	12944
50°	4205
55°	1456
60°	1253
65°	988
70°	611
75°	807
80°	0
85°	0



TEST NUMBER: P573160

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.5	11.5
10°-20°	379.7	28.7
20°-30°	441.4	33.4
30°-40°	270.3	20.4
40°-50°	67.1	5.1
50°-60°	7.9	0.6
60°-70°	2.9	0.2
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.7	73.6
0°-40°	1244.0	94.0
0°-60°	1319.0	99.7
0°-90°	1323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1656	
5°	1634	153
15°	1363	380
25°	977	441
35°	423	270
45°	74	67
55°	7	8
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P573160

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-M-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

0°	
0°	1655.7
2.5°	1654.0
5°	1633.7
7.5°	1589.6
10°	1530.4
12.5°	1452.5
15°	1362.8
17.5°	1266.3
20°	1171.5
22.5°	1076.7
25°	976.8
27.5°	861.7
30°	729.6
32.5°	575.6
35°	423.2
37.5°	297.9
40°	203.2
42.5°	126.9
45°	74.5
47.5°	42.3
50°	22.0
52.5°	10.2
55°	6.8
57.5°	5.1
60°	5.1
62.5°	3.4
65°	3.4
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)