

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573165

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1964.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573165

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573165

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302944
5°	296197
10°	273873
15°	245739
20°	216319
25°	186170
30°	149917
35°	99809
40°	51913
45°	23507
50°	10206
55°	6854
60°	4374
65°	3110
70°	2550
75°	1709
80°	0
85°	0



TEST NUMBER: P573165

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.5	11.3
10°-20°	539.7	27.5
20°-30°	626.6	31.9
30°-40°	414.9	21.1
40°-50°	116.4	5.9
50°-60°	29.3	1.5
60°-70°	11.0	0.6
70°-80°	3.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.7	70.7
0°-40°	1803.6	91.8
0°-60°	1949.3	99.2
0°-90°	1964.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1964.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2466	
5°	2402	222
15°	1932	540
25°	1373	627
35°	666	415
45°	135	116
55°	32	29
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P573165

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	2465.9
2.5°	2455.2
5°	2401.8
7.5°	2309.2
10°	2195.4
12.5°	2067.2
15°	1932.1
17.5°	1800.4
20°	1654.6
22.5°	1519.4
25°	1373.4
27.5°	1234.7
30°	1056.8
32.5°	868.2
35°	665.5
37.5°	476.8
40°	323.7
42.5°	209.9
45°	135.3
47.5°	81.9
50°	53.4
52.5°	39.1
55°	32.0
57.5°	25.0
60°	17.8
62.5°	14.3
65°	10.7
67.5°	7.1
70°	7.1
72.5°	3.6
75°	3.6
77.5°	3.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)