

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572204

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 714.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572204

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P572204

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56537
5°	56753
10°	56923
15°	56929
20°	56623
25°	55292
30°	51679
35°	44753
40°	34961
45°	25088
50°	16303
55°	9746
60°	5700
65°	3663
70°	2443
75°	1851
80°	1344
85°	0



TEST NUMBER: P572204

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.8	6.1
10°-20°	126.3	17.7
20°-30°	186.4	26.1
30°-40°	183.9	25.8
40°-50°	112.6	15.8
50°-60°	43.1	6.0
60°-70°	13.5	1.9
70°-80°	3.9	0.6
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.5	49.9
0°-40°	540.4	75.7
0°-60°	696.1	97.5
0°-90°	714.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	714.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	460	44
15°	448	126
25°	408	186
35°	298	184
45°	144	113
55°	46	43
65°	13	13
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P572204

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	460.2
2.5°	461.2
5°	460.2
7.5°	459.2
10°	456.3
12.5°	452.5
15°	447.6
17.5°	441.8
20°	433.1
22.5°	423.4
25°	407.9
27.5°	388.5
30°	364.3
32.5°	334.3
35°	298.4
37.5°	258.7
40°	218.0
42.5°	180.2
45°	144.4
47.5°	112.4
50°	85.3
52.5°	63.0
55°	45.5
57.5°	32.0
60°	23.2
62.5°	17.5
65°	12.6
67.5°	9.7
70°	6.8
72.5°	4.8
75°	3.9
77.5°	1.9
80°	1.9
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)