

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573189

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2367.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573189

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573189

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	288337
5°	284148
10°	272276
15°	257173
20°	240048
25°	217916
30°	181934
35°	131799
40°	82512
45°	47153
50°	24598
55°	13772
60°	8772
65°	5203
70°	3843
75°	1709
80°	2547
85°	0



TEST NUMBER: P573189

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.0	9.1
10°-20°	566.6	23.9
20°-30°	728.1	30.8
30°-40°	547.8	23.1
40°-50°	220.0	9.3
50°-60°	62.5	2.6
60°-70°	19.8	0.8
70°-80°	5.6	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1510.7	63.8
0°-40°	2058.5	87.0
0°-60°	2341.1	98.9
0°-90°	2367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2347	
5°	2304	216
15°	2022	567
25°	1608	728
35°	879	548
45°	271	220
55°	64	63
65°	18	20
75°	4	6
85°	0	0
90°	0	



TEST NUMBER: P573189

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-M-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	2347.0
2.5°	2332.7
5°	2304.1
7.5°	2250.5
10°	2182.6
12.5°	2100.6
15°	2022.0
17.5°	1932.6
20°	1836.1
22.5°	1732.7
25°	1607.6
27.5°	1457.5
30°	1282.5
32.5°	1086.0
35°	878.8
37.5°	685.8
40°	514.5
42.5°	378.7
45°	271.4
47.5°	185.8
50°	128.7
52.5°	89.3
55°	64.3
57.5°	46.5
60°	35.7
62.5°	25.0
65°	17.9
67.5°	14.3
70°	10.7
72.5°	7.1
75°	3.6
77.5°	3.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)