

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572248

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-30 F4X-W-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-30 F4X-W-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 400.0 lumens
Efficiency: N/A
Efficacy: 41.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572248

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-W-X-LI-BL89AM

Luminous Intensity Polar Plot



TEST NUMBER: P572248

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-W-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92				
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84				
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77				
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64				
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58				
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54				
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49				
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45				
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30111
5°	30621
10°	31998
15°	33972
20°	35456
25°	35149
30°	32684
35°	27971
40°	21298
45°	12492
50°	5332
55°	1564
60°	442
65°	262
70°	180
75°	237
80°	0
85°	0



TEST NUMBER: P572248

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-W-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.0	6.0
10°-20°	75.6	18.9
20°-30°	118.0	29.5
30°-40°	114.8	28.7
40°-50°	57.3	14.3
50°-60°	8.9	2.2
60°-70°	1.1	0.3
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.6	54.4
0°-40°	332.4	83.1
0°-60°	398.6	99.7
0°-90°	400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	245	
5°	248	24
15°	267	76
25°	259	118
35°	186	115
45°	72	57
55°	7	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P572248

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-30 F4X-W-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	245.1
2.5°	246.0
5°	248.3
7.5°	252.0
10°	256.5
12.5°	262.5
15°	267.1
17.5°	270.7
20°	271.2
22.5°	268.0
25°	259.3
27.5°	246.5
30°	230.4
32.5°	210.3
35°	186.5
37.5°	160.3
40°	132.8
42.5°	103.5
45°	71.9
47.5°	46.3
50°	27.9
52.5°	15.1
55°	7.3
57.5°	3.2
60°	1.8
62.5°	1.4
65°	0.9
67.5°	0.9
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)