

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573215

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2862.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573215

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573215

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226628
5°	227493
10°	228190
15°	228199
20°	226948
25°	221630
30°	207142
35°	179387
40°	140135
45°	100544
50°	65308
55°	39089
60°	22875
65°	14680
70°	9770
75°	7357
80°	5518
85°	0



TEST NUMBER: P573215

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.7	6.1
10°-20°	506.2	17.7
20°-30°	747.0	26.1
30°-40°	737.1	25.8
40°-50°	451.1	15.8
50°-60°	172.9	6.0
60°-70°	54.1	1.9
70°-80°	15.8	0.6
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1428.8	49.9
0°-40°	2165.9	75.7
0°-60°	2789.9	97.5
0°-90°	2862.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2862.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1845	
5°	1845	176
15°	1794	506
25°	1635	747
35°	1196	737
45°	579	451
55°	182	173
65°	50	54
75°	16	16
85°	0	2
90°	0	



TEST NUMBER: P573215

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1844.7
2.5°	1848.6
5°	1844.7
7.5°	1840.8
10°	1829.2
12.5°	1813.6
15°	1794.2
17.5°	1770.9
20°	1735.9
22.5°	1697.2
25°	1635.0
27.5°	1557.2
30°	1460.2
32.5°	1339.9
35°	1196.1
37.5°	1036.9
40°	873.8
42.5°	722.3
45°	578.7
47.5°	450.4
50°	341.7
52.5°	252.5
55°	182.5
57.5°	128.1
60°	93.1
62.5°	70.0
65°	50.5
67.5°	38.9
70°	27.2
72.5°	19.4
75°	15.5
77.5°	7.8
80°	7.8
82.5°	3.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)