

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573224

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2383.0 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573224

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573224

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290290
5°	286072
10°	274123
15°	258902
20°	241669
25°	219380
30°	183168
35°	132699
40°	83058
45°	47483
50°	24751
55°	13879
60°	8845
65°	5233
70°	3879
75°	1709
80°	2547
85°	0



TEST NUMBER: P573224

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.4	9.1
10°-20°	570.4	23.9
20°-30°	733.1	30.8
30°-40°	551.5	23.1
40°-50°	221.5	9.3
50°-60°	63.0	2.6
60°-70°	19.9	0.8
70°-80°	5.7	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1520.9	63.8
0°-40°	2072.4	87.0
0°-60°	2356.9	98.9
0°-90°	2383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2363	
5°	2320	217
15°	2036	570
25°	1618	733
35°	885	552
45°	273	222
55°	65	63
65°	18	20
75°	4	6
85°	0	0
90°	0	



TEST NUMBER: P573224

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2362.9
2.5°	2348.5
5°	2319.7
7.5°	2265.7
10°	2197.4
12.5°	2114.8
15°	2035.6
17.5°	1945.7
20°	1848.5
22.5°	1744.4
25°	1618.4
27.5°	1467.3
30°	1291.2
32.5°	1093.3
35°	884.8
37.5°	690.5
40°	517.9
42.5°	381.2
45°	273.3
47.5°	187.1
50°	129.5
52.5°	89.9
55°	64.8
57.5°	46.8
60°	36.0
62.5°	25.2
65°	18.0
67.5°	14.4
70°	10.8
72.5°	7.2
75°	3.6
77.5°	3.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)