

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571667

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 257.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571667

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P571667

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20357
5°	20435
10°	20496
15°	20490
20°	20382
25°	19899
30°	18598
35°	16107
40°	12589
45°	9035
50°	5868
55°	3513
60°	2064
65°	1308
70°	862
75°	665
80°	495
85°	0



TEST NUMBER: P571667

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.8	6.1
10°-20°	45.5	17.7
20°-30°	67.1	26.1
30°-40°	66.2	25.8
40°-50°	40.5	15.8
50°-60°	15.5	6.0
60°-70°	4.9	1.9
70°-80°	1.4	0.5
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.3	49.9
0°-40°	194.5	75.7
0°-60°	250.5	97.5
0°-90°	257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	166	
5°	166	16
15°	161	45
25°	147	67
35°	107	66
45°	52	41
55°	16	16
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P571667

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	165.7
2.5°	166.0
5°	165.7
7.5°	165.3
10°	164.3
12.5°	162.9
15°	161.1
17.5°	159.0
20°	155.9
22.5°	152.4
25°	146.8
27.5°	139.8
30°	131.1
32.5°	120.3
35°	107.4
37.5°	93.1
40°	78.5
42.5°	64.9
45°	52.0
47.5°	40.4
50°	30.7
52.5°	22.7
55°	16.4
57.5°	11.5
60°	8.4
62.5°	6.3
65°	4.5
67.5°	3.5
70°	2.4
72.5°	1.7
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)