

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571669

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 289.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571669

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P571669

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	105		110	108	105	103		104	102	100			100	98	97			96
2	106	101	97	93		104	99	95	92		96	93	90			93	90	88			90
3	100	93	87	83		98	92	86	82		89	85	81			86	83	80			84
4	94	86	79	75		92	84	79	74		82	77	73			80	76	72			78
5	88	79	72	68		87	78	72	67		76	71	67			74	70	66			73
6	83	73	66	62		82	72	66	61		71	65	61			69	64	60			68
7	78	68	61	56		77	67	61	56		66	60	56			64	59	55			63
8	74	63	56	52		72	62	56	51		61	55	51			60	55	51			59
9	69	59	52	48		68	58	52	47		57	51	47			56	51	47			55
10	66	55	48	44		65	54	48	44		53	48	44			53	47	44			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21757
5°	22124
10°	23128
15°	24547
20°	25612
25°	25389
30°	23620
35°	20202
40°	15396
45°	9035
50°	3861
55°	1135
60°	319
65°	203
70°	108
75°	142
80°	0
85°	0



TEST NUMBER: P571669

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.3	6.0
10°-20°	54.6	18.9
20°-30°	85.2	29.5
30°-40°	82.9	28.7
40°-50°	41.4	14.3
50°-60°	6.4	2.2
60°-70°	0.8	0.3
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.2	54.4
0°-40°	240.1	83.1
0°-60°	288.0	99.7
0°-90°	289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	289.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	177	
5°	179	17
15°	193	55
25°	187	85
35°	135	83
45°	52	41
55°	5	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P571669

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	177.1
2.5°	177.7
5°	179.4
7.5°	182.0
10°	185.4
12.5°	189.6
15°	193.0
17.5°	195.6
20°	195.9
22.5°	193.6
25°	187.3
27.5°	178.1
30°	166.5
32.5°	151.9
35°	134.7
37.5°	115.8
40°	96.0
42.5°	74.8
45°	52.0
47.5°	33.4
50°	20.2
52.5°	10.9
55°	5.3
57.5°	2.3
60°	1.3
62.5°	1.0
65°	0.7
67.5°	0.7
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)