

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573256

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1427.0 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573256

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89AM

Luminous Intensity Polar Plot



TEST NUMBER: P573256

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92						
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84						
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77						
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70						
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64						
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58						
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54						
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49						
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45						
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107411
5°	109239
10°	114170
15°	121184
20°	126489
25°	125387
30°	116608
35°	99764
40°	76001
45°	44582
50°	19055
55°	5612
60°	1597
65°	959
70°	575
75°	759
80°	0
85°	0



TEST NUMBER: P573256

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	6.0
10°-20°	269.8	18.9
20°-30°	420.9	29.5
30°-40°	409.6	28.7
40°-50°	204.6	14.3
50°-60°	31.7	2.2
60°-70°	3.8	0.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.3	54.4
0°-40°	1185.9	83.1
0°-60°	1422.1	99.7
0°-90°	1427.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	874	
5°	886	86
15°	953	270
25°	925	421
35°	665	410
45°	257	205
55°	26	32
65°	3	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P573256

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	874.3
2.5°	877.6
5°	885.8
7.5°	898.9
10°	915.2
12.5°	936.4
15°	952.8
17.5°	965.9
20°	967.5
22.5°	956.1
25°	925.0
27.5°	879.2
30°	822.0
32.5°	750.2
35°	665.2
37.5°	572.0
40°	473.9
42.5°	369.4
45°	256.6
47.5°	165.0
50°	99.7
52.5°	53.9
55°	26.2
57.5°	11.5
60°	6.5
62.5°	4.9
65°	3.3
67.5°	3.3
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)