

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571673

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 304.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571673

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P571673

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22888
5°	23271
10°	24326
15°	25819
20°	26945
25°	26718
30°	24840
35°	21252
40°	16198
45°	9504
50°	4052
55°	1199
60°	344
65°	203
70°	108
75°	142
80°	0
85°	0



TEST NUMBER: P571673

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	6.0
10°-20°	57.5	18.9
20°-30°	89.7	29.5
30°-40°	87.2	28.7
40°-50°	43.6	14.3
50°-60°	6.7	2.2
60°-70°	0.8	0.3
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.4	54.4
0°-40°	252.6	83.1
0°-60°	303.0	99.7
0°-90°	304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	186	
5°	189	18
15°	203	57
25°	197	90
35°	142	87
45°	55	44
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P571673

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	186.3
2.5°	187.0
5°	188.7
7.5°	191.5
10°	195.0
12.5°	199.5
15°	203.0
17.5°	205.8
20°	206.1
22.5°	203.7
25°	197.1
27.5°	187.3
30°	175.1
32.5°	159.8
35°	141.7
37.5°	121.8
40°	101.0
42.5°	78.7
45°	54.7
47.5°	35.2
50°	21.2
52.5°	11.5
55°	5.6
57.5°	2.4
60°	1.4
62.5°	1.0
65°	0.7
67.5°	0.7
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)