

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573257

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3460.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573257

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P573257

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92						
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84						
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77						
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70						
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64						
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58						
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54						
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49						
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45						
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260437
5°	264860
10°	276833
15°	293828
20°	306698
25°	304034
30°	282739
35°	241882
40°	184286
45°	108102
50°	46195
55°	13601
60°	3907
65°	2296
70°	1437
75°	1899
80°	0
85°	0



TEST NUMBER: P573257

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.3	6.0
10°-20°	654.3	18.9
20°-30°	1020.6	29.5
30°-40°	993.1	28.7
40°-50°	496.0	14.3
50°-60°	76.8	2.2
60°-70°	9.3	0.3
70°-80°	2.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1882.2	54.4
0°-40°	2875.3	83.1
0°-60°	3448.1	99.7
0°-90°	3460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2120	
5°	2148	207
15°	2310	654
25°	2243	1021
35°	1613	993
45°	622	496
55°	64	77
65°	8	9
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P573257

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2119.9
2.5°	2127.9
5°	2147.7
7.5°	2179.4
10°	2219.1
12.5°	2270.5
15°	2310.2
17.5°	2341.9
20°	2345.9
22.5°	2318.1
25°	2242.9
27.5°	2131.8
30°	1993.1
32.5°	1818.9
35°	1612.8
37.5°	1386.8
40°	1149.1
42.5°	895.6
45°	622.2
47.5°	400.2
50°	241.7
52.5°	130.7
55°	63.5
57.5°	27.8
60°	15.9
62.5°	11.9
65°	7.9
67.5°	7.9
70°	4.0
72.5°	4.0
75°	4.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)