

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571702

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 110.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571702

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P571702

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	61	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8710
5°	8744
10°	8770
15°	8776
20°	8720
25°	8513
30°	7958
35°	6899
40°	5389
45°	3857
50°	2504
55°	1499
60°	885
65°	552
70°	359
75°	285
80°	212
85°	0



TEST NUMBER: P571702

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.8	6.1
10°-20°	19.5	17.7
20°-30°	28.7	26.1
30°-40°	28.3	25.8
40°-50°	17.3	15.8
50°-60°	6.6	6.0
60°-70°	2.1	1.9
70°-80°	0.6	0.5
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	54.9	49.9
0°-40°	83.3	75.7
0°-60°	107.2	97.5
0°-90°	110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	71	
5°	71	7
15°	69	19
25°	63	29
35°	46	28
45°	22	17
55°	7	7
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P571702

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	70.9
2.5°	71.1
5°	70.9
7.5°	70.8
10°	70.3
12.5°	69.7
15°	69.0
17.5°	68.1
20°	66.7
22.5°	65.2
25°	62.8
27.5°	59.9
30°	56.1
32.5°	51.5
35°	46.0
37.5°	39.9
40°	33.6
42.5°	27.8
45°	22.2
47.5°	17.3
50°	13.1
52.5°	9.7
55°	7.0
57.5°	4.9
60°	3.6
62.5°	2.7
65°	1.9
67.5°	1.5
70°	1.0
72.5°	0.7
75°	0.6
77.5°	0.3
80°	0.3
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)