

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571713

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 224.0 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571713

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P571713

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27286
5°	26897
10°	25773
15°	24331
20°	22722
25°	20618
30°	17222
35°	12478
40°	7810
45°	4465
50°	2332
55°	1307
60°	835
65°	494
70°	359
75°	142
80°	212
85°	0



TEST NUMBER: P571713

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	9.1
10°-20°	53.6	23.9
20°-30°	68.9	30.8
30°-40°	51.9	23.1
40°-50°	20.8	9.3
50°-60°	5.9	2.7
60°-70°	1.9	0.8
70°-80°	0.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.0	63.8
0°-40°	194.8	87.0
0°-60°	221.6	98.9
0°-90°	224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	222	
5°	218	20
15°	191	54
25°	152	69
35°	83	52
45°	26	21
55°	6	6
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P571713

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-M-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	222.1
2.5°	220.8
5°	218.1
7.5°	213.0
10°	206.6
12.5°	198.8
15°	191.3
17.5°	182.9
20°	173.8
22.5°	164.0
25°	152.1
27.5°	137.9
30°	121.4
32.5°	102.8
35°	83.2
37.5°	64.9
40°	48.7
42.5°	35.8
45°	25.7
47.5°	17.6
50°	12.2
52.5°	8.5
55°	6.1
57.5°	4.4
60°	3.4
62.5°	2.4
65°	1.7
67.5°	1.4
70°	1.0
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)