

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571732

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 98.1 lumens
Efficiency: N/A
Efficacy: 28.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571732

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P571732

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	91		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	85		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30984
5°	27883
10°	21619
15°	15644
20°	10838
25°	7903
30°	5731
35°	3389
40°	1427
45°	452
50°	57
55°	43
60°	49
65°	58
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P571732

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	20.3
10°-20°	34.0	34.7
20°-30°	27.1	27.6
30°-40°	14.3	14.6
40°-50°	2.5	2.5
50°-60°	0.2	0.2
60°-70°	0.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	81.0	82.6
0°-40°	95.3	97.1
0°-60°	97.9	99.9
0°-90°	98.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	98.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	252	
5°	226	20
15°	123	34
25°	58	27
35°	23	14
45°	3	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P571732

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	252.2
2.5°	245.7
5°	226.1
7.5°	200.4
10°	173.3
12.5°	147.0
15°	123.0
17.5°	100.7
20°	82.9
22.5°	69.3
25°	58.3
27.5°	49.4
30°	40.4
32.5°	31.4
35°	22.6
37.5°	14.9
40°	8.9
42.5°	5.1
45°	2.6
47.5°	0.9
50°	0.3
52.5°	0.3
55°	0.2
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)