

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573305

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3671.9 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573305

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P573305

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94						
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82						
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76						
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71						
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67						
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63						
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59						
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55						
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	564549
5°	559182
10°	529883
15°	481073
20°	425107
25°	367513
30°	287279
35°	176177
40°	90419
45°	35930
50°	11659
55°	4027
60°	3440
65°	2762
70°	1688
75°	2231
80°	0
85°	0



TEST NUMBER: P573305

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	423.3	11.5
10°-20°	1053.9	28.7
20°-30°	1225.2	33.4
30°-40°	750.2	20.4
40°-50°	186.3	5.1
50°-60°	21.7	0.6
60°-70°	8.1	0.2
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2702.4	73.6
0°-40°	3452.7	94.0
0°-60°	3660.7	99.7
0°-90°	3671.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3671.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4595	
5°	4534	423
15°	3782	1054
25°	2711	1225
35°	1175	750
45°	207	186
55°	19	22
65°	10	8
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573305

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	4595.3
2.5°	4590.6
5°	4534.3
7.5°	4412.1
10°	4247.6
12.5°	4031.5
15°	3782.4
17.5°	3514.6
20°	3251.6
22.5°	2988.3
25°	2711.2
27.5°	2391.7
30°	2025.1
32.5°	1597.5
35°	1174.7
37.5°	826.9
40°	563.8
42.5°	352.3
45°	206.8
47.5°	117.5
50°	61.0
52.5°	28.2
55°	18.8
57.5°	14.0
60°	14.0
62.5°	9.5
65°	9.5
67.5°	4.7
70°	4.7
72.5°	4.7
75°	4.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)