

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571735

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-35 F4X-W-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-35 F4X-W-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 258.1 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571735

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P571735

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	63	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		56	52	48
9	67	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20431
5°	20509
10°	20571
15°	20566
20°	20460
25°	19981
30°	18669
35°	16167
40°	12637
45°	9069
50°	5887
55°	3534
60°	2064
65°	1337
70°	898
75°	665
80°	495
85°	0



TEST NUMBER: P571735

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.8	6.1
10°-20°	45.6	17.7
20°-30°	67.3	26.1
30°-40°	66.5	25.8
40°-50°	40.7	15.8
50°-60°	15.6	6.0
60°-70°	4.9	1.9
70°-80°	1.4	0.6
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.8	49.9
0°-40°	195.3	75.7
0°-60°	251.5	97.5
0°-90°	258.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	166	
5°	166	16
15°	162	46
25°	147	67
35°	108	66
45°	52	41
55°	16	16
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P571735

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	166.3
2.5°	166.6
5°	166.3
7.5°	165.9
10°	164.9
12.5°	163.5
15°	161.7
17.5°	159.6
20°	156.5
22.5°	153.0
25°	147.4
27.5°	140.4
30°	131.6
32.5°	120.8
35°	107.8
37.5°	93.5
40°	78.8
42.5°	65.1
45°	52.2
47.5°	40.6
50°	30.8
52.5°	22.8
55°	16.5
57.5°	11.5
60°	8.4
62.5°	6.3
65°	4.6
67.5°	3.5
70°	2.5
72.5°	1.8
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)