

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573319

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-30 F4X-W-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-30 F4X-W-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3109.9 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573319

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573319

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246272
5°	247213
10°	247963
15°	247977
20°	246611
25°	240838
30°	225102
35°	194924
40°	152275
45°	109248
50°	70965
55°	42474
60°	24866
65°	15959
70°	10632
75°	8022
80°	5943
85°	0



TEST NUMBER: P573319

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.9	6.1
10°-20°	550.1	17.7
20°-30°	811.7	26.1
30°-40°	801.0	25.8
40°-50°	490.2	15.8
50°-60°	187.9	6.0
60°-70°	58.7	1.9
70°-80°	17.2	0.6
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1552.6	49.9
0°-40°	2353.6	75.7
0°-60°	3031.7	97.5
0°-90°	3109.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3109.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2005	
5°	2005	191
15°	1950	550
25°	1777	812
35°	1300	801
45°	629	490
55°	198	188
65°	55	59
75°	17	17
85°	0	2
90°	0	



TEST NUMBER: P573319

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2004.6
2.5°	2008.8
5°	2004.6
7.5°	2000.4
10°	1987.7
12.5°	1970.8
15°	1949.7
17.5°	1924.3
20°	1886.3
22.5°	1844.3
25°	1776.7
27.5°	1692.2
30°	1586.8
32.5°	1456.0
35°	1299.7
37.5°	1126.7
40°	949.5
42.5°	784.9
45°	628.8
47.5°	489.4
50°	371.3
52.5°	274.4
55°	198.3
57.5°	139.2
60°	101.2
62.5°	76.0
65°	54.9
67.5°	42.2
70°	29.6
72.5°	21.1
75°	16.9
77.5°	8.4
80°	8.4
82.5°	4.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)