

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573356

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3007.0 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573356

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573356

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104		110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91		103	98	93	90		95	91	88			91	88	86			89
3	99	91	85	80		97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	72		90	82	76	71		80	75	70			78	73	70			76
5	87	77	70	65		85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	58		80	70	63	58		68	62	58			67	61	57			65
7	76	65	58	53		75	65	58	53		63	57	53			62	56	52			61
8	72	60	53	49		70	60	53	49		59	53	48			58	52	48			57
9	68	56	49	45		66	56	49	45		55	49	44			54	48	44			53
10	64	52	46	41		63	52	46	41		51	45	41			50	45	41			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238115
5°	239024
10°	239755
15°	239761
20°	238440
25°	232854
30°	217640
35°	188475
40°	147223
45°	105635
50°	68614
55°	41081
60°	24030
65°	15436
70°	10273
75°	7737
80°	5801
85°	0



TEST NUMBER: P573356

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	6.1
10°-20°	531.8	17.7
20°-30°	784.8	26.1
30°-40°	774.5	25.8
40°-50°	473.9	15.8
50°-60°	181.7	6.0
60°-70°	56.8	1.9
70°-80°	16.7	0.6
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1501.2	49.9
0°-40°	2275.7	75.7
0°-60°	2931.3	97.5
0°-90°	3007.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3007.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1938	
5°	1938	185
15°	1885	532
25°	1718	785
35°	1257	774
45°	608	474
55°	192	182
65°	53	57
75°	16	17
85°	0	2
90°	0	



TEST NUMBER: P573356

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	1938.2
2.5°	1942.3
5°	1938.2
7.5°	1934.1
10°	1921.9
12.5°	1905.5
15°	1885.1
17.5°	1860.6
20°	1823.8
22.5°	1783.2
25°	1717.8
27.5°	1636.1
30°	1534.2
32.5°	1407.8
35°	1256.7
37.5°	1089.4
40°	918.0
42.5°	758.9
45°	608.0
47.5°	473.2
50°	359.0
52.5°	265.3
55°	191.8
57.5°	134.6
60°	97.8
62.5°	73.5
65°	53.1
67.5°	40.8
70°	28.6
72.5°	20.4
75°	16.3
77.5°	8.2
80°	8.2
82.5°	4.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)