

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571773

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-40 F4X-W-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-40 F4X-W-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571773

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-40 F4X-W-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P571773

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-40 F4X-W-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	67	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19718
5°	19793
10°	19848
15°	19854
20°	19741
25°	19276
30°	18016
35°	15613
40°	12188
45°	8739
50°	5676
55°	3406
60°	1990
65°	1279
70°	862
75°	665
80°	495
85°	0



TEST NUMBER: P571773

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-40 F4X-W-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.3	6.1
10°-20°	44.0	17.7
20°-30°	65.0	26.1
30°-40°	64.1	25.8
40°-50°	39.2	15.8
50°-60°	15.0	6.0
60°-70°	4.7	1.9
70°-80°	1.4	0.6
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	124.3	49.9
0°-40°	188.4	75.7
0°-60°	242.7	97.5
0°-90°	249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	160	
5°	160	15
15°	156	44
25°	142	65
35°	104	64
45°	50	39
55°	16	15
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P571773

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-40 F4X-W-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	160.5
2.5°	160.8
5°	160.5
7.5°	160.2
10°	159.1
12.5°	157.8
15°	156.1
17.5°	154.1
20°	151.0
22.5°	147.7
25°	142.2
27.5°	135.5
30°	127.0
32.5°	116.6
35°	104.1
37.5°	90.2
40°	76.0
42.5°	62.8
45°	50.3
47.5°	39.2
50°	29.7
52.5°	22.0
55°	15.9
57.5°	11.1
60°	8.1
62.5°	6.1
65°	4.4
67.5°	3.4
70°	2.4
72.5°	1.7
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)