

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573359

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3318.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573359

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573359

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262734
5°	263738
10°	264542
15°	264562
20°	263110
25°	256942
30°	240153
35°	207957
40°	162459
45°	116563
50°	75724
55°	45322
60°	26536
65°	17035
70°	11315
75°	8544
80°	6367
85°	0



TEST NUMBER: P573359

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.7	6.1
10°-20°	586.8	17.7
20°-30°	866.0	26.1
30°-40°	854.6	25.8
40°-50°	523.0	15.8
50°-60°	200.5	6.0
60°-70°	62.7	1.9
70°-80°	18.4	0.6
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1656.5	49.9
0°-40°	2511.0	75.7
0°-60°	3234.5	97.5
0°-90°	3318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3318.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2139	
5°	2139	204
15°	2080	587
25°	1896	866
35°	1387	855
45°	671	523
55°	212	200
65°	59	63
75°	18	18
85°	0	2
90°	0	



TEST NUMBER: P573359

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-35 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2138.6
2.5°	2143.2
5°	2138.6
7.5°	2134.1
10°	2120.6
12.5°	2102.6
15°	2080.1
17.5°	2053.0
20°	2012.5
22.5°	1967.6
25°	1895.5
27.5°	1805.4
30°	1692.9
32.5°	1553.4
35°	1386.6
37.5°	1202.1
40°	1013.0
42.5°	837.4
45°	670.9
47.5°	522.2
50°	396.2
52.5°	292.7
55°	211.6
57.5°	148.5
60°	108.0
62.5°	81.1
65°	58.6
67.5°	45.1
70°	31.5
72.5°	22.5
75°	18.0
77.5°	9.0
80°	9.0
82.5°	4.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)