

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573387

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2689.9 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573387

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573387

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	850453
5°	765316
10°	593292
15°	429422
20°	297337
25°	216764
30°	157506
35°	93195
40°	39195
45°	12214
50°	1586
55°	878
60°	1007
65°	1192
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573387

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	545.5	20.3
10°-20°	934.0	34.7
20°-30°	742.3	27.6
30°-40°	392.9	14.6
40°-50°	67.7	2.5
50°-60°	5.0	0.2
60°-70°	2.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2221.8	82.6
0°-40°	2614.7	97.2
0°-60°	2687.4	99.9
0°-90°	2689.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2689.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6922	
5°	6206	546
15°	3376	934
25°	1599	742
35°	621	393
45°	70	68
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573387

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	6922.5
2.5°	6744.3
5°	6205.8
7.5°	5501.6
10°	4755.9
12.5°	4035.1
15°	3376.3
17.5°	2763.2
20°	2274.3
22.5°	1901.5
25°	1599.1
27.5°	1354.7
30°	1110.3
32.5°	861.7
35°	621.4
37.5°	410.2
40°	244.4
42.5°	140.9
45°	70.3
47.5°	24.9
50°	8.3
52.5°	8.3
55°	4.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)