

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573399

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3618.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573399

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573399

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272329
5°	276958
10°	289467
15°	307246
20°	320700
25°	317914
30°	295662
35°	252920
40°	192705
45°	113036
50°	48298
55°	14222
60°	4079
65°	2413
70°	1473
75°	1946
80°	0
85°	0



TEST NUMBER: P573399

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.8	6.0
10°-20°	684.1	18.9
20°-30°	1067.3	29.5
30°-40°	1038.4	28.7
40°-50°	518.7	14.3
50°-60°	80.3	2.2
60°-70°	9.7	0.3
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1968.2	54.4
0°-40°	3006.6	83.1
0°-60°	3605.6	99.7
0°-90°	3618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2217	
5°	2246	217
15°	2416	684
25°	2345	1067
35°	1686	1038
45°	651	519
55°	66	80
65°	8	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P573399

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	2216.7
2.5°	2225.0
5°	2245.8
7.5°	2279.0
10°	2320.4
12.5°	2374.2
15°	2415.7
17.5°	2448.9
20°	2453.0
22.5°	2424.0
25°	2345.3
27.5°	2229.2
30°	2084.2
32.5°	1902.0
35°	1686.4
37.5°	1450.2
40°	1201.6
42.5°	936.5
45°	650.6
47.5°	418.5
50°	252.7
52.5°	136.7
55°	66.4
57.5°	29.0
60°	16.6
62.5°	12.4
65°	8.3
67.5°	8.3
70°	4.1
72.5°	4.1
75°	4.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)