

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573403

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-50 F4X-M-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-50 F4X-M-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2900.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573403

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-M-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573403

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-M-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	353265
5°	348140
10°	333590
15°	315081
20°	294108
25°	266987
30°	222903
35°	161480
40°	101084
45°	57786
50°	30121
55°	16878
60°	10762
65°	6366
70°	4706
75°	2089
80°	3113
85°	0



TEST NUMBER: P573403

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-M-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.6	9.1
10°-20°	694.2	23.9
20°-30°	892.1	30.8
30°-40°	671.2	23.1
40°-50°	269.6	9.3
50°-60°	76.6	2.6
60°-70°	24.3	0.8
70°-80°	6.9	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1850.8	63.8
0°-40°	2522.0	87.0
0°-60°	2868.2	98.9
0°-90°	2900.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2900.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2876	
5°	2823	265
15°	2477	694
25°	1970	892
35°	1077	671
45°	333	270
55°	79	77
65°	22	24
75°	4	7
85°	0	1
90°	0	



TEST NUMBER: P573403

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-M-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2875.5
2.5°	2858.0
5°	2823.0
7.5°	2757.3
10°	2674.1
12.5°	2573.6
15°	2477.3
17.5°	2367.8
20°	2249.6
22.5°	2122.8
25°	1969.6
27.5°	1785.7
30°	1571.3
32.5°	1330.5
35°	1076.7
37.5°	840.3
40°	630.3
42.5°	463.9
45°	332.6
47.5°	227.7
50°	157.6
52.5°	109.5
55°	78.8
57.5°	56.9
60°	43.8
62.5°	30.7
65°	21.9
67.5°	17.5
70°	13.1
72.5°	8.8
75°	4.4
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)