

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572897

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2498.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572897

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P572897

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92						
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84						
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77						
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70						
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64						
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58						
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54						
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49						
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45						
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188027
5°	191224
10°	199860
15°	212136
20°	221431
25°	219502
30°	204135
35°	174633
40°	133046
45°	78044
50°	33352
55°	9810
60°	2826
65°	1657
70°	1042
75°	1377
80°	0
85°	0



TEST NUMBER: P572897

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.7	6.0
10°-20°	472.4	18.9
20°-30°	736.9	29.5
30°-40°	717.0	28.7
40°-50°	358.1	14.3
50°-60°	55.5	2.2
60°-70°	6.7	0.3
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1358.9	54.4
0°-40°	2075.9	83.1
0°-60°	2489.4	99.7
0°-90°	2498.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2498.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1530	
5°	1551	150
15°	1668	472
25°	1619	737
35°	1164	717
45°	449	358
55°	46	55
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P572897

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1530.5
2.5°	1536.2
5°	1550.6
7.5°	1573.5
10°	1602.1
12.5°	1639.2
15°	1667.9
17.5°	1690.8
20°	1693.7
22.5°	1673.6
25°	1619.3
27.5°	1539.1
30°	1439.0
32.5°	1313.2
35°	1164.4
37.5°	1001.2
40°	829.6
42.5°	646.6
45°	449.2
47.5°	288.9
50°	174.5
52.5°	94.4
55°	45.8
57.5°	20.1
60°	11.5
62.5°	8.6
65°	5.7
67.5°	5.7
70°	2.9
72.5°	2.9
75°	2.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)