

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572914

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-27 F4X-N-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-27 F4X-N-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 708.0 lumens
Efficiency: N/A
Efficacy: 22.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572914

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-N-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P572914

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-N-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	76	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109204
5°	106773
10°	98726
15°	88586
20°	77985
25°	67113
30°	54048
35°	35979
40°	18716
45°	8479
50°	3670
55°	2463
60°	1573
65°	1134
70°	934
75°	617
80°	0
85°	0



TEST NUMBER: P572914

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-N-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.2	11.3
10°-20°	194.5	27.5
20°-30°	225.9	31.9
30°-40°	149.6	21.1
40°-50°	42.0	5.9
50°-60°	10.5	1.5
60°-70°	4.0	0.6
70°-80°	1.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.6	70.7
0°-40°	650.2	91.8
0°-60°	702.7	99.2
0°-90°	708.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	889	
5°	866	80
15°	696	195
25°	495	226
35°	240	150
45°	49	42
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572914

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-N-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	888.9
2.5°	885.1
5°	865.8
7.5°	832.4
10°	791.4
12.5°	745.2
15°	696.5
17.5°	649.0
20°	596.5
22.5°	547.7
25°	495.1
27.5°	445.1
30°	381.0
32.5°	313.0
35°	239.9
37.5°	171.9
40°	116.7
42.5°	75.7
45°	48.8
47.5°	29.5
50°	19.2
52.5°	14.1
55°	11.5
57.5°	9.0
60°	6.4
62.5°	5.1
65°	3.9
67.5°	2.6
70°	2.6
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)