

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573467

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3643.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573467

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573467

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	288472
5°	289574
10°	290452
15°	290470
20°	288879
25°	282115
30°	263673
35°	228339
40°	178368
45°	127978
50°	83140
55°	49756
60°	29116
65°	18692
70°	12428
75°	9398
80°	7004
85°	0



TEST NUMBER: P573467

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.6	6.1
10°-20°	644.3	17.7
20°-30°	950.8	26.1
30°-40°	938.3	25.8
40°-50°	574.2	15.8
50°-60°	220.1	6.0
60°-70°	68.8	1.9
70°-80°	20.2	0.6
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1818.7	49.9
0°-40°	2757.0	75.7
0°-60°	3551.3	97.5
0°-90°	3643.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3643.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2348	
5°	2348	224
15°	2284	644
25°	2081	951
35°	1522	938
45°	737	574
55°	232	220
65°	64	69
75°	20	20
85°	0	3
90°	0	



TEST NUMBER: P573467

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2348.1
2.5°	2353.1
5°	2348.1
7.5°	2343.2
10°	2328.3
12.5°	2308.5
15°	2283.8
17.5°	2254.1
20°	2209.6
22.5°	2160.3
25°	2081.2
27.5°	1982.2
30°	1858.7
32.5°	1705.5
35°	1522.5
37.5°	1319.8
40°	1112.2
42.5°	919.5
45°	736.6
47.5°	573.3
50°	435.0
52.5°	321.4
55°	232.3
57.5°	163.1
60°	118.5
62.5°	89.1
65°	64.3
67.5°	49.5
70°	34.6
72.5°	24.7
75°	19.8
77.5°	9.9
80°	9.9
82.5°	4.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)