

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572929

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2587.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572929

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P572929

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194723
5°	198032
10°	206983
15°	219691
20°	229314
25°	227324
30°	211398
35°	180857
40°	137793
45°	80824
50°	34536
55°	10174
60°	2924
65°	1715
70°	1078
75°	1424
80°	0
85°	0



TEST NUMBER: P572929

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	6.0
10°-20°	489.2	18.9
20°-30°	763.1	29.5
30°-40°	742.5	28.7
40°-50°	370.9	14.3
50°-60°	57.4	2.2
60°-70°	6.9	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1407.3	54.4
0°-40°	2149.8	83.1
0°-60°	2578.1	99.7
0°-90°	2587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1585	
5°	1606	155
15°	1727	489
25°	1677	763
35°	1206	743
45°	465	371
55°	48	57
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P572929

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1585.0
2.5°	1591.0
5°	1605.8
7.5°	1629.5
10°	1659.2
12.5°	1697.6
15°	1727.3
17.5°	1751.0
20°	1754.0
22.5°	1733.2
25°	1677.0
27.5°	1593.9
30°	1490.2
32.5°	1360.0
35°	1205.9
37.5°	1036.9
40°	859.2
42.5°	669.6
45°	465.2
47.5°	299.2
50°	180.7
52.5°	97.8
55°	47.5
57.5°	20.8
60°	11.9
62.5°	8.9
65°	5.9
67.5°	5.9
70°	3.0
72.5°	3.0
75°	3.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)