

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573469

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4102.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573469

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573469

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	105		110	108	105	103		104	102	100			100	98	97			96
2	106	101	97	93		104	99	95	92		96	93	90			93	90	88			90
3	100	93	87	83		98	92	86	82		89	85	81			86	83	80			84
4	94	86	79	75		92	84	79	74		82	77	73			80	76	72			78
5	88	79	72	68		87	78	72	67		76	71	67			74	70	66			73
6	83	73	66	62		82	72	66	61		71	65	61			69	64	60			68
7	78	68	61	56		77	67	61	56		66	60	56			64	59	55			63
8	74	63	56	52		72	62	56	51		61	55	51			60	55	51			59
9	69	59	52	48		68	58	52	47		57	51	47			56	51	47			55
10	66	55	48	44		65	54	48	44		53	48	44			53	47	44			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	308768
5°	314004
10°	328201
15°	348341
20°	363608
25°	360451
30°	335213
35°	286770
40°	218493
45°	128151
50°	54758
55°	16128
60°	4619
65°	2733
70°	1688
75°	2231
80°	0
85°	0



TEST NUMBER: P573469

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.8	6.0
10°-20°	775.7	18.9
20°-30°	1210.0	29.5
30°-40°	1177.4	28.7
40°-50°	588.1	14.3
50°-60°	91.0	2.2
60°-70°	11.0	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2231.5	54.4
0°-40°	3408.8	83.1
0°-60°	4087.9	99.7
0°-90°	4102.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4102.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2513	
5°	2546	246
15°	2739	776
25°	2659	1210
35°	1912	1177
45°	738	588
55°	75	91
65°	9	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573469

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	2513.3
2.5°	2522.7
5°	2546.2
7.5°	2583.8
10°	2630.9
12.5°	2691.8
15°	2738.8
17.5°	2776.5
20°	2781.2
22.5°	2748.2
25°	2659.1
27.5°	2527.4
30°	2363.0
32.5°	2156.4
35°	1912.1
37.5°	1644.2
40°	1362.4
42.5°	1061.8
45°	737.6
47.5°	474.4
50°	286.5
52.5°	155.0
55°	75.3
57.5°	32.9
60°	18.8
62.5°	14.1
65°	9.4
67.5°	9.4
70°	4.7
72.5°	4.7
75°	4.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)