

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572951

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1785.9 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572951

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P572951

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275487
5°	269349
10°	249048
15°	223468
20°	196721
25°	169293
30°	136326
35°	90751
40°	47214
45°	21370
50°	9270
55°	6233
60°	3980
65°	2820
70°	2335
75°	1519
80°	0
85°	0



TEST NUMBER: P572951

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.3	11.3
10°-20°	490.8	27.5
20°-30°	569.8	31.9
30°-40°	377.3	21.1
40°-50°	105.8	5.9
50°-60°	26.6	1.5
60°-70°	10.0	0.6
70°-80°	3.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1262.8	70.7
0°-40°	1640.2	91.8
0°-60°	1772.6	99.3
0°-90°	1785.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1785.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2242	
5°	2184	202
15°	1757	491
25°	1249	570
35°	605	377
45°	123	106
55°	29	27
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P572951

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2242.4
2.5°	2232.7
5°	2184.1
7.5°	2099.9
10°	1996.4
12.5°	1879.9
15°	1757.0
17.5°	1637.3
20°	1504.7
22.5°	1381.7
25°	1248.9
27.5°	1122.8
30°	961.0
32.5°	789.5
35°	605.1
37.5°	433.6
40°	294.4
42.5°	190.8
45°	123.0
47.5°	74.5
50°	48.5
52.5°	35.5
55°	29.1
57.5°	22.7
60°	16.2
62.5°	13.0
65°	9.7
67.5°	6.5
70°	6.5
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)