

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572955

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1933.1 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572955

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P572955

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	611122
5°	549945
10°	426329
15°	308582
20°	213665
25°	155765
30°	113175
35°	66979
40°	28162
45°	8791
50°	1147
55°	643
60°	737
65°	872
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P572955

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	392.0	20.3
10°-20°	671.1	34.7
20°-30°	533.4	27.6
30°-40°	282.4	14.6
40°-50°	48.6	2.5
50°-60°	3.7	0.2
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1596.5	82.6
0°-40°	1878.9	97.2
0°-60°	1931.2	99.9
0°-90°	1933.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1933.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4974	
5°	4459	392
15°	2426	671
25°	1149	533
35°	447	282
45°	51	49
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P572955

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-N-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	4974.4
2.5°	4846.4
5°	4459.4
7.5°	3953.4
10°	3417.5
12.5°	2899.6
15°	2426.2
17.5°	1985.6
20°	1634.3
22.5°	1366.4
25°	1149.1
27.5°	973.5
30°	797.8
32.5°	619.2
35°	446.6
37.5°	294.8
40°	175.6
42.5°	101.2
45°	50.6
47.5°	17.9
50°	6.0
52.5°	6.0
55°	3.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	3.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)