

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572962

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 985.0 lumens
Efficiency: N/A
Efficacy: 31.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572962

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P572962

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78000
5°	78298
10°	78529
15°	78538
20°	78103
25°	76276
30°	71298
35°	61730
40°	48224
45°	34609
50°	22476
55°	13451
60°	7863
65°	5058
70°	3376
75°	2563
80°	1910
85°	0



TEST NUMBER: P572962

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	6.1
10°-20°	174.2	17.7
20°-30°	257.1	26.1
30°-40°	253.7	25.8
40°-50°	155.2	15.8
50°-60°	59.5	6.0
60°-70°	18.6	1.9
70°-80°	5.5	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.7	49.9
0°-40°	745.4	75.7
0°-60°	960.2	97.5
0°-90°	985.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	985.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	635	
5°	635	60
15°	618	174
25°	563	257
35°	412	254
45°	199	155
55°	63	60
65°	17	19
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P572962

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-30 F4X-W-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	634.9
2.5°	636.2
5°	634.9
7.5°	633.6
10°	629.5
12.5°	624.2
15°	617.5
17.5°	609.5
20°	597.4
22.5°	584.1
25°	562.7
27.5°	535.9
30°	502.6
32.5°	461.1
35°	411.6
37.5°	356.9
40°	300.7
42.5°	248.6
45°	199.2
47.5°	155.0
50°	117.6
52.5°	86.9
55°	62.8
57.5°	44.1
60°	32.0
62.5°	24.1
65°	17.4
67.5°	13.4
70°	9.4
72.5°	6.7
75°	5.4
77.5°	2.7
80°	2.7
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)