

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573484

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89AM**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573484  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-45-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89AM  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBMLI TRIM  
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1753.1 lumens  
Efficiency: N/A  
Efficacy: 35.3 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573484

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89AM

### Luminous Intensity Polar Plot





TEST NUMBER: P573484

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89AM

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 111 | 109 | 106 |  | 111 | 109 | 107 | 105 |  | 105 | 103 | 101 |  | 101 | 100 | 98  |  | 98  | 97  | 96  |
| 2   | 108 | 103 | 100 | 96  |  | 106 | 102 | 98  | 95  |  | 99  | 96  | 93  |  | 96  | 93  | 91  |  | 93  | 91  | 89  |
| 3   | 103 | 97  | 92  | 88  |  | 101 | 95  | 91  | 87  |  | 93  | 89  | 86  |  | 90  | 87  | 85  |  | 88  | 85  | 83  |
| 4   | 98  | 91  | 85  | 81  |  | 96  | 89  | 84  | 81  |  | 87  | 83  | 80  |  | 85  | 82  | 79  |  | 83  | 80  | 78  |
| 5   | 93  | 85  | 79  | 75  |  | 91  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 73  |  | 79  | 76  | 73  |
| 6   | 89  | 80  | 74  | 70  |  | 87  | 79  | 74  | 70  |  | 78  | 73  | 69  |  | 76  | 72  | 69  |  | 75  | 71  | 68  |
| 7   | 84  | 75  | 69  | 65  |  | 83  | 75  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 68  | 64  |  | 71  | 67  | 64  |
| 8   | 80  | 71  | 65  | 61  |  | 79  | 70  | 65  | 61  |  | 69  | 64  | 61  |  | 68  | 64  | 60  |  | 67  | 63  | 60  |
| 9   | 77  | 67  | 61  | 57  |  | 75  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  | 60  | 57  |  | 64  | 60  | 57  |
| 10  | 73  | 64  | 58  | 54  |  | 72  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  | 57  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 269516 |
| 5°  | 266957 |
| 10° | 252965 |
| 15° | 229662 |
| 20° | 202945 |
| 25° | 175447 |
| 30° | 137149 |
| 35° | 84107  |
| 40° | 43173  |
| 45° | 17148  |
| 50° | 5562   |
| 55° | 1928   |
| 60° | 1646   |
| 65° | 1308   |
| 70° | 826    |
| 75° | 1092   |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P573484

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89AM

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 202.1  | 11.5      |
| 10°-20°   | 503.2  | 28.7      |
| 20°-30°   | 584.9  | 33.4      |
| 30°-40°   | 358.2  | 20.4      |
| 40°-50°   | 88.9   | 5.1       |
| 50°-60°   | 10.4   | 0.6       |
| 60°-70°   | 3.9    | 0.2       |
| 70°-80°   | 1.5    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1290.1 | 73.6      |
| 0°-40°    | 1648.3 | 94.0      |
| 0°-60°    | 1747.7 | 99.7      |
| 0°-90°    | 1753.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1753.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2194 |      |
| 5°  | 2165 | 202  |
| 15° | 1806 | 503  |
| 25° | 1294 | 585  |
| 35° | 561  | 358  |
| 45° | 99   | 89   |
| 55° | 9    | 10   |
| 65° | 4    | 4    |
| 75° | 2    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P573484

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-M-X-LI-BL89AM

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2193.8 |
| 2.5°  | 2191.5 |
| 5°    | 2164.7 |
| 7.5°  | 2106.3 |
| 10°   | 2027.8 |
| 12.5° | 1924.6 |
| 15°   | 1805.7 |
| 17.5° | 1677.9 |
| 20°   | 1552.3 |
| 22.5° | 1426.6 |
| 25°   | 1294.3 |
| 27.5° | 1141.8 |
| 30°   | 966.8  |
| 32.5° | 762.7  |
| 35°   | 560.8  |
| 37.5° | 394.8  |
| 40°   | 269.2  |
| 42.5° | 168.2  |
| 45°   | 98.7   |
| 47.5° | 56.1   |
| 50°   | 29.1   |
| 52.5° | 13.5   |
| 55°   | 9.0    |
| 57.5° | 6.7    |
| 60°   | 6.7    |
| 62.5° | 4.5    |
| 65°   | 4.5    |
| 67.5° | 2.3    |
| 70°   | 2.3    |
| 72.5° | 2.3    |
| 75°   | 2.3    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)