

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573499

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3601.0 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573499

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573499

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104		110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91		103	98	93	90		95	91	88			91	88	86			89
3	99	91	85	80		97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	72		90	82	76	71		80	75	70			78	73	70			76
5	87	77	70	65		85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	58		80	70	63	58		68	62	58			67	61	57			65
7	76	65	58	53		75	65	58	53		63	57	53			62	56	52			61
8	72	60	53	49		70	60	53	49		59	53	48			58	52	48			57
9	68	56	49	45		66	56	49	45		55	49	44			54	48	44			53
10	64	52	46	41		63	52	46	41		51	45	41			50	45	41			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285155
5°	286244
10°	287109
15°	287125
20°	285545
25°	278861
30°	260637
35°	225699
40°	176315
45°	126501
50°	82184
55°	49199
60°	28797
65°	18488
70°	12285
75°	9304
80°	6933
85°	0



TEST NUMBER: P573499

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	6.1
10°-20°	636.9	17.7
20°-30°	939.8	26.1
30°-40°	927.5	25.8
40°-50°	567.6	15.8
50°-60°	217.6	6.0
60°-70°	68.0	1.9
70°-80°	20.0	0.6
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1797.8	49.9
0°-40°	2725.2	75.7
0°-60°	3510.4	97.5
0°-90°	3601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2321	
5°	2321	221
15°	2258	637
25°	2057	940
35°	1505	927
45°	728	568
55°	230	218
65°	64	68
75°	20	20
85°	0	3
90°	0	



TEST NUMBER: P573499

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-H-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	2321.1
2.5°	2326.0
5°	2321.1
7.5°	2316.2
10°	2301.5
12.5°	2281.9
15°	2257.5
17.5°	2228.1
20°	2184.1
22.5°	2135.4
25°	2057.2
27.5°	1959.3
30°	1837.3
32.5°	1685.9
35°	1504.9
37.5°	1304.6
40°	1099.4
42.5°	908.9
45°	728.1
47.5°	566.7
50°	430.0
52.5°	317.7
55°	229.7
57.5°	161.2
60°	117.2
62.5°	88.0
65°	63.6
67.5°	48.9
70°	34.2
72.5°	24.5
75°	19.6
77.5°	9.8
80°	9.8
82.5°	4.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)