

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573027

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1963.0 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573027

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573027

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			90
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			85
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			81
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			77
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			73
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			69
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			66
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			63
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	620607
5°	558479
10°	432953
15°	313364
20°	216986
25°	158178
30°	114934
35°	68014
40°	28611
45°	8913
50°	1166
55°	643
60°	737
65°	872
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573027

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	398.1	20.3
10°-20°	681.5	34.7
20°-30°	541.7	27.6
30°-40°	286.7	14.6
40°-50°	49.4	2.5
50°-60°	3.7	0.2
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1621.3	82.6
0°-40°	1908.0	97.2
0°-60°	1961.2	99.9
0°-90°	1963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1963.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5052	
5°	4529	398
15°	2464	682
25°	1167	542
35°	454	287
45°	51	49
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573027

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	5051.6
2.5°	4921.6
5°	4528.6
7.5°	4014.7
10°	3470.6
12.5°	2944.6
15°	2463.8
17.5°	2016.4
20°	1659.7
22.5°	1387.6
25°	1166.9
27.5°	988.6
30°	810.2
32.5°	628.8
35°	453.5
37.5°	299.3
40°	178.4
42.5°	102.8
45°	51.3
47.5°	18.2
50°	6.1
52.5°	6.1
55°	3.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	3.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)