

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573040

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-40 F4X-W-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-40 F4X-W-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1185.0 lumens
Efficiency: N/A
Efficacy: 37.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573040

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-W-X-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573040

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-W-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89192
5°	90716
10°	94809
15°	100631
20°	105035
25°	104132
30°	96833
35°	82847
40°	63123
45°	37024
50°	15825
55°	4648
60°	1327
65°	785
70°	503
75°	665
80°	0
85°	0



TEST NUMBER: P573040

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-W-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.0	6.0
10°-20°	224.1	18.9
20°-30°	349.6	29.5
30°-40°	340.1	28.7
40°-50°	169.9	14.3
50°-60°	26.3	2.2
60°-70°	3.2	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	644.6	54.4
0°-40°	984.8	83.1
0°-60°	1180.9	99.7
0°-90°	1185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1185.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	726	
5°	736	71
15°	791	224
25°	768	350
35°	552	340
45°	213	170
55°	22	26
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P573040

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-W-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	726.0
2.5°	728.8
5°	735.6
7.5°	746.4
10°	760.0
12.5°	777.6
15°	791.2
17.5°	802.1
20°	803.4
22.5°	793.9
25°	768.2
27.5°	730.1
30°	682.6
32.5°	623.0
35°	552.4
37.5°	475.0
40°	393.6
42.5°	306.7
45°	213.1
47.5°	137.1
50°	82.8
52.5°	44.8
55°	21.7
57.5°	9.5
60°	5.4
62.5°	4.1
65°	2.7
67.5°	2.7
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)