

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573044

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-50 F4X-M-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-50 F4X-M-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2018.9 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573044

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573044

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245953
5°	242379
10°	232245
15°	219360
20°	204762
25°	185871
30°	155194
35°	112422
40°	70372
45°	40221
50°	20967
55°	11759
60°	7494
65°	4419
70°	3269
75°	1424
80°	2122
85°	0



TEST NUMBER: P573044

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.2	9.1
10°-20°	483.3	23.9
20°-30°	621.1	30.8
30°-40°	467.3	23.1
40°-50°	187.7	9.3
50°-60°	53.3	2.6
60°-70°	16.9	0.8
70°-80°	4.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1288.6	63.8
0°-40°	1755.9	87.0
0°-60°	1996.9	98.9
0°-90°	2018.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2018.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2002	
5°	1965	184
15°	1725	483
25°	1371	621
35°	750	467
45°	232	188
55°	55	53
65°	15	17
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P573044

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2002.0
2.5°	1989.8
5°	1965.4
7.5°	1919.7
10°	1861.7
12.5°	1791.8
15°	1724.7
17.5°	1648.5
20°	1566.2
22.5°	1477.9
25°	1371.2
27.5°	1243.2
30°	1094.0
32.5°	926.3
35°	749.6
37.5°	585.0
40°	438.8
42.5°	323.0
45°	231.5
47.5°	158.5
50°	109.7
52.5°	76.2
55°	54.9
57.5°	39.6
60°	30.5
62.5°	21.3
65°	15.2
67.5°	12.2
70°	9.1
72.5°	6.1
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)