

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573533

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3383.0 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573533

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573533

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1069550
5°	962485
10°	746134
15°	540050
20°	373937
25°	272612
30°	198078
35°	117207
40°	49299
45°	15376
50°	1988
55°	1114
60°	1278
65°	1512
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573533

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	686.1	20.3
10°-20°	1174.6	34.7
20°-30°	933.5	27.6
30°-40°	494.2	14.6
40°-50°	85.1	2.5
50°-60°	6.4	0.2
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2794.1	82.6
0°-40°	3288.3	97.2
0°-60°	3379.8	99.9
0°-90°	3383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8706	
5°	7805	686
15°	4246	1175
25°	2011	933
35°	782	494
45°	88	85
55°	5	6
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573533

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	8705.9
2.5°	8481.8
5°	7804.6
7.5°	6918.9
10°	5981.1
12.5°	5074.6
15°	4246.1
17.5°	3475.0
20°	2860.2
22.5°	2391.3
25°	2011.1
27.5°	1703.7
30°	1396.3
32.5°	1083.7
35°	781.5
37.5°	515.9
40°	307.4
42.5°	177.2
45°	88.5
47.5°	31.3
50°	10.4
52.5°	10.4
55°	5.2
57.5°	5.2
60°	5.2
62.5°	5.2
65°	5.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)