

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573545

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4550.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573545

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573545

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	342491
5°	348300
10°	364042
15°	386395
20°	403313
25°	399816
30°	371812
35°	318085
40°	242357
45°	142155
50°	60740
55°	17885
60°	5135
65°	3023
70°	1868
75°	2468
80°	0
85°	0



TEST NUMBER: P573545

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.6	6.0
10°-20°	860.4	18.9
20°-30°	1342.2	29.5
30°-40°	1305.9	28.7
40°-50°	652.3	14.3
50°-60°	101.0	2.2
60°-70°	12.2	0.3
70°-80°	3.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2475.2	54.4
0°-40°	3781.1	83.1
0°-60°	4534.3	99.7
0°-90°	4550.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4550.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2788	
5°	2824	273
15°	3038	860
25°	2950	1342
35°	2121	1306
45°	818	652
55°	84	101
65°	10	12
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573545

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2787.8
2.5°	2798.2
5°	2824.3
7.5°	2866.0
10°	2918.2
12.5°	2985.8
15°	3038.0
17.5°	3079.7
20°	3084.9
22.5°	3048.4
25°	2949.5
27.5°	2803.4
30°	2621.0
32.5°	2391.9
35°	2120.9
37.5°	1823.7
40°	1511.2
42.5°	1177.7
45°	818.2
47.5°	526.2
50°	317.8
52.5°	171.9
55°	83.5
57.5°	36.5
60°	20.9
62.5°	15.7
65°	10.4
67.5°	10.4
70°	5.2
72.5°	5.2
75°	5.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)