

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573070

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1021.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573070

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573070

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104		110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91		103	98	93	90		95	91	88			91	88	86			89
3	99	91	85	80		97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	72		90	82	76	71		80	75	70			78	73	70			76
5	87	77	70	65		85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	58		80	70	63	58		68	62	58			67	61	57			65
7	76	65	58	53		75	65	58	53		63	57	53			62	56	52			61
8	72	60	53	49		70	60	53	49		59	53	48			58	52	48			57
9	68	56	49	45		66	56	49	45		55	49	44			54	48	44			53
10	64	52	46	41		63	52	46	41		51	45	41			50	45	41			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80850
5°	81159
10°	81399
15°	81413
20°	80966
25°	79069
30°	73894
35°	63995
40°	49989
45°	35860
50°	23298
55°	13944
60°	8157
65°	5233
70°	3484
75°	2611
80°	1981
85°	0



TEST NUMBER: P573070

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.7	6.1
10°-20°	180.6	17.7
20°-30°	266.5	26.1
30°-40°	263.0	25.8
40°-50°	160.9	15.8
50°-60°	61.7	6.0
60°-70°	19.3	1.9
70°-80°	5.6	0.6
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.7	49.9
0°-40°	772.7	75.7
0°-60°	995.3	97.5
0°-90°	1021.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1021.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	658	
5°	658	63
15°	640	181
25°	583	266
35°	427	263
45°	206	161
55°	65	62
65°	18	19
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P573070

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	658.1
2.5°	659.5
5°	658.1
7.5°	656.7
10°	652.5
12.5°	647.0
15°	640.1
17.5°	631.7
20°	619.3
22.5°	605.5
25°	583.3
27.5°	555.5
30°	520.9
32.5°	478.0
35°	426.7
37.5°	369.9
40°	311.7
42.5°	257.7
45°	206.4
47.5°	160.7
50°	121.9
52.5°	90.1
55°	65.1
57.5°	45.7
60°	33.2
62.5°	25.0
65°	18.0
67.5°	13.9
70°	9.7
72.5°	6.9
75°	5.5
77.5°	2.8
80°	2.8
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)