

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573562

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1186.0 lumens
Efficiency: N/A
Efficacy: 23.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573562

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573562

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		76	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182941
5°	178867
10°	165379
15°	148402
20°	130633
25°	112428
30°	90534
35°	60261
40°	31353
45°	14195
50°	6154
55°	4134
60°	2654
65°	1890
70°	1545
75°	1044
80°	0
85°	0



TEST NUMBER: P573562

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	11.3
10°-20°	325.9	27.5
20°-30°	378.4	31.9
30°-40°	250.6	21.1
40°-50°	70.3	5.9
50°-60°	17.7	1.5
60°-70°	6.6	0.6
70°-80°	2.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.6	70.7
0°-40°	1089.2	91.8
0°-60°	1177.1	99.2
0°-90°	1186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1489	
5°	1450	134
15°	1167	326
25°	829	378
35°	402	251
45°	82	70
55°	19	18
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P573562

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	1489.1
2.5°	1482.6
5°	1450.4
7.5°	1394.5
10°	1325.7
12.5°	1248.3
15°	1166.8
17.5°	1087.2
20°	999.2
22.5°	917.5
25°	829.4
27.5°	745.6
30°	638.2
32.5°	524.3
35°	401.8
37.5°	287.9
40°	195.5
42.5°	126.7
45°	81.7
47.5°	49.5
50°	32.2
52.5°	23.6
55°	19.3
57.5°	15.1
60°	10.8
62.5°	8.6
65°	6.5
67.5°	4.3
70°	4.3
72.5°	2.2
75°	2.2
77.5°	2.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)