

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573101

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573101  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-35-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBNI TRIM  
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2388.0 lumens  
Efficiency: N/A  
Efficacy: 59.1 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 40.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573101

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P573101

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |
| 2   | 109 | 105 | 102 | 99  |  | 107 | 103 | 100 | 98  |  | 100 | 98  | 95  |  | 97  | 95  | 93  |  | 95  | 93  | 92  |
| 3   | 105 | 99  | 95  | 92  |  | 103 | 98  | 94  | 91  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 89  | 87  |
| 4   | 101 | 94  | 89  | 86  |  | 99  | 93  | 88  | 85  |  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  |  | 95  | 88  | 84  | 80  |  | 87  | 82  | 79  |  | 85  | 81  | 79  |  | 83  | 80  | 78  |
| 6   | 92  | 85  | 80  | 76  |  | 91  | 84  | 79  | 76  |  | 83  | 78  | 75  |  | 81  | 78  | 75  |  | 80  | 77  | 74  |
| 7   | 89  | 81  | 76  | 72  |  | 88  | 80  | 75  | 72  |  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |
| 8   | 85  | 77  | 72  | 68  |  | 84  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |
| 9   | 82  | 74  | 69  | 65  |  | 81  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 67  | 64  |
| 10  | 79  | 71  | 66  | 62  |  | 78  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 69  | 65  | 62  |  | 68  | 64  | 62  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 754971 |
| 5°  | 679397 |
| 10° | 526689 |
| 15° | 381206 |
| 20° | 263960 |
| 25° | 192432 |
| 30° | 139816 |
| 35° | 82742  |
| 40° | 34801  |
| 45° | 10841  |
| 50° | 1414   |
| 55° | 792    |
| 60° | 909    |
| 65° | 1076   |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P573101

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 484.3  | 20.3      |
| 10°-20°   | 829.1  | 34.7      |
| 20°-30°   | 658.9  | 27.6      |
| 30°-40°   | 348.8  | 14.6      |
| 40°-50°   | 60.1   | 2.5       |
| 50°-60°   | 4.5    | 0.2       |
| 60°-70°   | 2.3    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1972.3 | 82.6      |
| 0°-40°    | 2321.2 | 97.2      |
| 0°-60°    | 2385.8 | 99.9      |
| 0°-90°    | 2388.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2388.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6145 |      |
| 5°  | 5509 | 484  |
| 15° | 2997 | 829  |
| 25° | 1420 | 659  |
| 35° | 552  | 349  |
| 45° | 62   | 60   |
| 55° | 4    | 5    |
| 65° | 4    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P573101

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 6145.3 |
| 2.5°  | 5987.1 |
| 5°    | 5509.1 |
| 7.5°  | 4884.0 |
| 10°   | 4222.0 |
| 12.5° | 3582.1 |
| 15°   | 2997.2 |
| 17.5° | 2452.9 |
| 20°   | 2019.0 |
| 22.5° | 1688.0 |
| 25°   | 1419.6 |
| 27.5° | 1202.6 |
| 30°   | 985.6  |
| 32.5° | 765.0  |
| 35°   | 551.7  |
| 37.5° | 364.1  |
| 40°   | 217.0  |
| 42.5° | 125.1  |
| 45°   | 62.4   |
| 47.5° | 22.1   |
| 50°   | 7.4    |
| 52.5° | 7.4    |
| 55°   | 3.7    |
| 57.5° | 3.7    |
| 60°   | 3.7    |
| 62.5° | 3.7    |
| 65°   | 3.7    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)