

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573571

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3656.0 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573571

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573571

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289504
5°	290610
10°	291488
15°	291513
20°	289911
25°	283118
30°	264610
35°	229149
40°	179009
45°	128429
50°	83427
55°	49949
60°	29239
65°	18779
70°	12500
75°	9446
80°	7004
85°	0



TEST NUMBER: P573571

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.4	6.1
10°-20°	646.6	17.7
20°-30°	954.2	26.1
30°-40°	941.6	25.8
40°-50°	576.2	15.8
50°-60°	220.9	6.0
60°-70°	69.1	1.9
70°-80°	20.2	0.6
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1825.2	49.9
0°-40°	2766.8	75.7
0°-60°	3564.0	97.5
0°-90°	3656.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3656.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2356	
5°	2356	224
15°	2292	647
25°	2089	954
35°	1528	942
45°	739	576
55°	233	221
65°	65	69
75°	20	20
85°	0	3
90°	0	



TEST NUMBER: P573571

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2356.5
2.5°	2361.5
5°	2356.5
7.5°	2351.5
10°	2336.6
12.5°	2316.8
15°	2292.0
17.5°	2262.2
20°	2217.5
22.5°	2168.0
25°	2088.6
27.5°	1989.3
30°	1865.3
32.5°	1711.6
35°	1527.9
37.5°	1324.5
40°	1116.2
42.5°	922.7
45°	739.2
47.5°	575.4
50°	436.5
52.5°	322.6
55°	233.2
57.5°	163.6
60°	119.0
62.5°	89.4
65°	64.6
67.5°	49.7
70°	34.8
72.5°	24.8
75°	19.9
77.5°	9.9
80°	9.9
82.5°	5.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)