

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573109

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3053.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573109

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573109

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229810
5°	233709
10°	244270
15°	259259
20°	270614
25°	268275
30°	249487
35°	213431
40°	162619
45°	95384
50°	40748
55°	11995
60°	3440
65°	2035
70°	1257
75°	1661
80°	0
85°	0



TEST NUMBER: P573109

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.9	6.0
10°-20°	577.3	18.9
20°-30°	900.6	29.5
30°-40°	876.3	28.7
40°-50°	437.7	14.3
50°-60°	67.8	2.2
60°-70°	8.2	0.3
70°-80°	2.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.8	54.4
0°-40°	2537.1	83.1
0°-60°	3042.5	99.7
0°-90°	3053.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3053.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1871	
5°	1895	183
15°	2038	577
25°	1979	901
35°	1423	876
45°	549	438
55°	56	68
65°	7	8
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P573109

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-27 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1870.6
2.5°	1877.6
5°	1895.1
7.5°	1923.1
10°	1958.1
12.5°	2003.4
15°	2038.4
17.5°	2066.4
20°	2069.9
22.5°	2045.4
25°	1979.1
27.5°	1881.1
30°	1758.7
32.5°	1605.0
35°	1423.1
37.5°	1223.7
40°	1014.0
42.5°	790.2
45°	549.0
47.5°	353.1
50°	213.2
52.5°	115.4
55°	56.0
57.5°	24.5
60°	14.0
62.5°	10.5
65°	7.0
67.5°	7.0
70°	3.5
72.5°	3.5
75°	3.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)