

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573579

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4188.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573579

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573579

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315242
5°	320590
10°	335075
15°	355654
20°	371230
25°	368001
30°	342235
35°	292769
40°	223064
45°	130844
50°	55904
55°	16450
60°	4718
65°	2791
70°	1724
75°	2278
80°	0
85°	0



TEST NUMBER: P573579

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.9	6.0
10°-20°	791.9	18.9
20°-30°	1235.4	29.5
30°-40°	1202.0	28.7
40°-50°	600.4	14.3
50°-60°	92.9	2.2
60°-70°	11.2	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2278.3	54.4
0°-40°	3480.3	83.1
0°-60°	4173.6	99.7
0°-90°	4188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4188.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2566	
5°	2600	251
15°	2796	792
25°	2715	1235
35°	1952	1202
45°	753	600
55°	77	93
65°	10	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573579

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-W-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	2566.0
2.5°	2575.6
5°	2599.6
7.5°	2638.0
10°	2686.0
12.5°	2748.2
15°	2796.3
17.5°	2834.7
20°	2839.5
22.5°	2805.9
25°	2714.8
27.5°	2580.4
30°	2412.5
32.5°	2201.6
35°	1952.1
37.5°	1678.6
40°	1390.9
42.5°	1084.0
45°	753.1
47.5°	484.4
50°	292.5
52.5°	158.3
55°	76.8
57.5°	33.6
60°	19.2
62.5°	14.4
65°	9.6
67.5°	9.6
70°	4.8
72.5°	4.8
75°	4.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)