

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573129

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1937.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573129

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573129

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298780
5°	292127
10°	270106
15°	242368
20°	213351
25°	183608
30°	147860
35°	98430
40°	51207
45°	23177
50°	10053
55°	6747
60°	4324
65°	3081
70°	2514
75°	1661
80°	0
85°	0



TEST NUMBER: P573129

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.4	11.3
10°-20°	532.3	27.5
20°-30°	618.0	31.9
30°-40°	409.2	21.1
40°-50°	114.8	5.9
50°-60°	28.8	1.5
60°-70°	10.8	0.6
70°-80°	3.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1369.6	70.7
0°-40°	1778.9	91.8
0°-60°	1922.5	99.2
0°-90°	1937.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1937.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2432	
5°	2369	219
15°	1906	532
25°	1354	618
35°	656	409
45°	133	115
55°	32	29
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P573129

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	2432.0
2.5°	2421.4
5°	2368.8
7.5°	2277.5
10°	2165.2
12.5°	2038.8
15°	1905.6
17.5°	1775.7
20°	1631.9
22.5°	1498.5
25°	1354.5
27.5°	1217.8
30°	1042.3
32.5°	856.2
35°	656.3
37.5°	470.3
40°	319.3
42.5°	207.0
45°	133.4
47.5°	80.8
50°	52.6
52.5°	38.5
55°	31.5
57.5°	24.6
60°	17.6
62.5°	14.1
65°	10.6
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)