

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573130

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 869.0 lumens
Efficiency: N/A
Efficacy: 21.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573130

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573130

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	76	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134045
5°	131055
10°	121181
15°	108732
20°	95713
25°	82376
30°	66333
35°	44153
40°	22966
45°	10390
50°	4511
55°	3020
60°	1941
65°	1366
70°	1149
75°	759
80°	0
85°	0



TEST NUMBER: P573130

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.4	11.3
10°-20°	238.8	27.5
20°-30°	277.2	31.9
30°-40°	183.6	21.1
40°-50°	51.5	5.9
50°-60°	12.9	1.5
60°-70°	4.9	0.6
70°-80°	1.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.5	70.7
0°-40°	798.0	91.8
0°-60°	862.5	99.2
0°-90°	869.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	869.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1091	
5°	1063	98
15°	855	239
25°	608	277
35°	294	184
45°	60	51
55°	14	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P573130

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	1091.1
2.5°	1086.3
5°	1062.7
7.5°	1021.7
10°	971.4
12.5°	914.7
15°	854.9
17.5°	796.6
20°	732.1
22.5°	672.3
25°	607.7
27.5°	546.3
30°	467.6
32.5°	384.1
35°	294.4
37.5°	211.0
40°	143.2
42.5°	92.9
45°	59.8
47.5°	36.2
50°	23.6
52.5°	17.3
55°	14.1
57.5°	11.1
60°	7.9
62.5°	6.3
65°	4.7
67.5°	3.2
70°	3.2
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)