

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573140

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-30 F4X-W-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-30 F4X-W-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2555.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573140

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573140

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202327
5°	203100
10°	203715
15°	203716
20°	202605
25°	197854
30°	184927
35°	160145
40°	125092
45°	89755
50°	58313
55°	34891
60°	20418
65°	13110
70°	8729
75°	6598
80°	4882
85°	0



TEST NUMBER: P573140

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	6.1
10°-20°	451.9	17.7
20°-30°	666.8	26.1
30°-40°	658.0	25.8
40°-50°	402.7	15.8
50°-60°	154.4	6.0
60°-70°	48.3	1.9
70°-80°	14.2	0.6
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.6	49.9
0°-40°	1933.6	75.7
0°-60°	2490.7	97.5
0°-90°	2555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1647	
5°	1647	157
15°	1602	452
25°	1460	667
35°	1068	658
45°	517	403
55°	163	154
65°	45	48
75°	14	14
85°	0	2
90°	0	



TEST NUMBER: P573140

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	1646.9
2.5°	1650.3
5°	1646.9
7.5°	1643.4
10°	1633.0
12.5°	1619.1
15°	1601.7
17.5°	1580.9
20°	1549.7
22.5°	1515.1
25°	1459.6
27.5°	1390.2
30°	1303.6
32.5°	1196.2
35°	1067.8
37.5°	925.6
40°	780.0
42.5°	644.9
45°	516.6
47.5°	402.1
50°	305.1
52.5°	225.4
55°	162.9
57.5°	114.4
60°	83.1
62.5°	62.5
65°	45.1
67.5°	34.7
70°	24.3
72.5°	17.4
75°	13.9
77.5°	6.9
80°	6.9
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)