

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573625

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4402.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573625

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573625

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	101		101	100	98		98	97	96
2	108	103	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	85		88	85	83
4	98	91	85	81		96	89	84	81		87	83	80		85	82	79		83	80	78
5	93	85	79	75		91	84	79	75		82	78	74		81	77	73		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	69	65		83	75	69	65		73	68	65		72	68	64		71	67	64
8	80	71	65	61		79	70	65	61		69	64	61		68	64	60		67	63	60
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	676788
5°	670346
10°	635220
15°	576718
20°	509616
25°	440577
30°	344391
35°	211197
40°	108397
45°	43070
50°	13990
55°	4819
60°	4128
65°	3314
70°	2047
75°	2706
80°	0
85°	0



TEST NUMBER: P573625

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	507.5	11.5
10°-20°	1263.5	28.7
20°-30°	1468.7	33.4
30°-40°	899.4	20.4
40°-50°	223.4	5.1
50°-60°	26.1	0.6
60°-70°	9.8	0.2
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3239.7	73.6
0°-40°	4139.1	94.0
0°-60°	4388.5	99.7
0°-90°	4402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4402.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5509	
5°	5436	507
15°	4534	1263
25°	3250	1469
35°	1408	899
45°	248	223
55°	22	26
65°	11	10
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573625

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	5508.9
2.5°	5503.2
5°	5435.7
7.5°	5289.2
10°	5092.0
12.5°	4832.9
15°	4534.4
17.5°	4213.3
20°	3898.0
22.5°	3582.4
25°	3250.2
27.5°	2867.1
30°	2427.7
32.5°	1915.1
35°	1408.2
37.5°	991.3
40°	675.9
42.5°	422.4
45°	247.9
47.5°	140.9
50°	73.2
52.5°	33.8
55°	22.5
57.5°	16.8
60°	16.8
62.5°	11.4
65°	11.4
67.5°	5.7
70°	5.7
72.5°	5.7
75°	5.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)